

## Lumina

### Lumina Edge LED 2700K

### 3039986



#### Product features

- Ambient decorative Edge LED rectangular horizontal wall light with indirect lighting to provide a soft lighting effect, 2700K amber white colour temperature, white aluminium body and integrated LED (non-dimmable) driver, 620 lumens, 12W, 52lm/W, 2700K, IP20, RAL 9003



#### PRODUCT OVERVIEW

Product name	Lumina Edge LED 2700K
Technology	LED
Housing	Aluminium
Mount	Wall surface mounted
Environment	Internal
General application	Hospitality, Residential & Consumer
ETIM Class	EC002892
E-number FI	4271118
E-number SE	7502643
Warranty	3 years
Fixture luminous flux (lm)	620
Luminaire efficacy (lm/W)	52
LOR (%)	100
Colour temperature (K)	2700
Light colour	Amber White
CRI (Ra)	85
Total power consumption (W)	12
Electrical protection	Class II
Control gear type	LED driver constant current
Dimming method	N/A
Housing colour	White
IP rating	IP20
IK rating	IK02
Product EAN number	8711971399865

#### DATA TABLE

##### General data

Product name	Lumina Edge LED 2700K
Technology	LED
Housing	Aluminium
Mount	Wall surface mounted

## Lumina

*Lumina Edge LED 2700K*

3039986

Environment	Internal
General application	Hospitality, Residential & Consumer
Performance ambient temperature Tq (°C)	25
ETIM Class	EC002892
E-number FI	4271118
E-number SE	7502643
Warranty	3 years

### Optical data

Fixture luminous flux (lm)	620
Luminaire efficacy (lm/W)	52
LOR (%)	100
Colour temperature (K)	2700
Light colour	Amber White
CRI (Ra)	85
Adjustable chromaticity	N

### Electrical data

Total power consumption (W)	12
Mains voltage (V)	100-240V
Electrical protection	Class II
Control gear type	LED driver constant current
Transformer required	No
Dimming method	N/A
Drive current (mA)	350
Energy Efficiency Class (A->G) of contained light source	E

### Lifetime data

Lifespan L70 B50	50000
Lifespan L80 B20	35000
Lifespan L90 B10	25000

### Physical data

Housing colour	White
IP rating	IP20
IK rating	IK02
Diffuser finish	Opal
Diffuser material	PC Polycarbonate
Reflector finish	Other
Nominal Product Length (mm)	55
Nominal Product Width (mm)	78
Nominal Product Height (mm)	330
Weight (kg)	0.66


### Packaging

Single packaging type	Carton
Product EAN number	8711971399865

## Lumina Lumina Edge LED 2700K 3039986

Packaging single length / height (cm)	10.0
Packaging single width (cm)	6.2
Packaging single depth (cm)	33.6
DUN14 (outer)	18711971399862
Units per outer package	20
Packaging outer length / height (cm)	41.5
Packaging outer width (cm)	33.0
Packaging outer depth (cm)	35.0

### PHOTOMETRY



Distance [m]	Cone diameter [m]	E(0°) [lx]	E(C0) [lx]	E(C90) [lx]
0.5	1.58	832	64	64
1.0	3.15	208	16	16
1.5	4.73	92	7	7
2.0	6.30	52	4	4
2.5	7.88	33	3	3
3.0	9.45	23	2	2

Distance [m] Cone diameter [m]  
C0 - C180 (Half beam angle: 115.2°) Illuminance [lx]

### TECHNICAL DRAWINGS

