

Boring bar holder, shape E2

For turning tools with cylindrical shanks

ORION[®]

Execution:

- Surface hardness 58–60 HRC
- Core strength HV 950 N/mm²
- Hardness depth 0.8 mm ±0.2 mm
- Fully bronzed and precision-ground
- Internal and external coolant supply

Art. no.	22778 129
Brand	ORION
Manufacturer Part Number	22778129
VDI mount diameter	50 mm
Clamping diameter	40 mm
Length	30 mm
Outer diameter	98 mm
Projecting length	90 mm
Gross Weight	5.700 kg
Product Group	2AC



EAN

4053625465279

