

Workbench trolleys

Working height 840 mm, with 4 drawers and 1 door

Application:

The mobile workstation with versatile options for use.

Execution:

- Welded sheet steel construction equipped with one workbench top panel made of solid beechwood, 40 mm thick
- Suitable insert material for drawers, see from no. 50485 060-265 and from no. 50537 610-695
- Other equipment options available at extra cost: SOFT-CLOSE for drawers, see no. 50392 005, ELECTRONIC CODE combination lock, see no. 50392 010

Advantage:

- When you buy this product, you plant a tree and also receive a tree certificate!
- When you buy this product, you plant a tree and also receive a tree certificate!



Art. no.	50285 236
Brand	HK
Manufacturer Part Number	50285236
Number of fixed rollers	2 PCS
Working height	840 mm
Number of steering rollers	2 PCS
Worktop width	1155 mm
Number of drawers	4 PCS
Worktop height	40 mm
Number of doors	1 PCS
Worktop depth	700 mm
Pullout type	Partial extension
On castors	Yes
Moving device, can be lowered	No
Colour of front	Optional
Cabinet colour	Optional
With single pull-out safety brake	Yes
Surface	Powder-coated
With wheel lock	Yes
Load-carrying capacity	820 kg
Wheel diameter	200 mm
Type	mobile
Lock type	DOM® locking system
Material of worktop	Solid beech
Drawer front height	1 x 60 mm, 1 x 90 mm, 1 x 150 mm, 1 x 180 mm
Material	Sheet steel
Drawer width (inner dimension)	450 mm
Drawer width (inner dimension) x drawer depth (inner dimension)	450 x 600 mm
Drawer depth (inner dimension)	600 mm
Load-carrying capacity per drawer	100 kg
Material of wheel	Solid rubber
Central locking	Yes
Gross Weight	133.000 kg
Product Group	501

EAN

4039247875870