

Pneumatic blow-out and liquid gun, series 208

With fixed 90 mm tube



Application:

For cleaning work using compressed air, coolant or non-explosive water-based liquids.

Execution:

- Nozzle made of brass
- With infinite flow control

Advantage:

- Ergonomic handle piece for working comfortably
- High blowing force
- Infinitely adjustable air flow



Art. no.	75179 003
Brand	CEJN
Manufacturer Part Number	112080100
Model	With 90 mm, permanently attached pipe
Max. operating pressure	16 bar
Burst pressure	64 bar
Connection thread	R 1/4 inch
Sound-pressure level	96 dB
Min./max. temperature conditions	-20 to +60 °C
Weight	0.096 kg
Gross Weight	0.108 kg
Product Group	7AI

EAN

7391390118578