

PAC
PAC-ELCO20-F20-F20-8M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Similar to illustration

Pre-assembled PAC-ELCO cables are specially designed for connecting Weidmüller's RS-ELCO interfaces to controller devices.

The main features are:

- One end is connected to the RS-ELCO interface and the other end can be fitted with ELCO female headers or wire-end ferrules.
- Shielded cable with 0.25 mm² cross-section.
- Metal plug housing with side input and coding.
- Available in a variety of versions and lengths.

General ordering data

Type	PAC-ELCO20-F20-F20-8M
Order No.	7789760080
Version	Pre-assembled cable, PAC, Pre-assembled cable, Cable LiYCY, 0.25 mm ²
GTIN (EAN)	4032248345557
Qty.	1 pc(s).

PAC
PAC-ELCO20-F20-F20-8M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Net weight	1,884 g
------------	---------

Temperatures

Operating temperature, max.	50 °C	Operating temperature, min.	-10 °C
Storage temperature, max.	60 °C	Storage temperature, min.	-10 °C
Operating temperature	-10...50 °C	Storage temperature	-10...60 °C

General Data

Connector PLC side	Conector ELCO Female	Interface connector	Conector ELCO Female
Number of poles, min.	20-pole	Outer diameter	10.15 ± 1 mm
Cable	Cable LiYCY	Cable length	8 m
Material	PVC	Wire cross-section	0.25 mm ²

Electrical Data

Rated voltage (text)	250 V	Permissible current strength per path, max.	1 A
Total current, max.	3 A	Resistance	≤ 80 mΩ/m
High voltage test	1 KV/1s		

Classifications

ETIM 6.0	EC000237	eClass 6.2	27-24-92-05
eClass 8.1	27-24-92-05	eClass 9.0	27-24-22-20
eClass 9.1	27-24-22-20		

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	Colours chart
--------------------	-------------------------------