

## Coaxial Cable Connector 11\_N-50-4-10/133\_N

### Description

Straight cable plug

Interface standards

IEC 61169-16\_MIL-STD-348A/304\_CECC 22210



### Technical Data

#### Electrical Data

Impedance	50 Ω		
Interface frequency max.	11 GHz		
Frequency range	DC to 2 GHz	2 to 4 GHz	4 to 6 GHz
Return loss	32 dB	25.5 dB	24.6 dB

#### Mechanical Data

Centre contact	plugged
Outer contact	crimped

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Bronze	SUCOPRO Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

### Related Documents

Outline drawing	DOU-00083576
Assembly instruction	DOC-0000180145

### Ordering Information

Bulk 100 pcs package	11_N-50-4-10/133_NH
----------------------	---------------------

### Additional Information

Suitable cables	S_04162_B-01, SX_04172_B-60, S_04262_B-01, LMR-240
-----------------	--

### Remarks

Ingress protection according to IP66 with shrink tube with glue