

# TY5253MX



CABLE TIE 50LB 11 UV BLK 2-PC DIST



## General Information

Extended Product Type	TY5253MX
Product ID	7TAG009180R0007
EAN	5414363065593
Catalog Description	CABLE TIE 50LB 11 UV BLK 2-PC DIST
Long Description	Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (220 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 289.7mm (11.40 Inches), Width of 4.82mm (0.19 Inches), Thickness of 1.41mm (0.055 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds)

## Ordering

EAN	5414363065593
Customs Tariff Number	3926909990

## Dimensions

Product Net Weight	.005 lb 2.268 g
--------------------	--------------------

## Container Information

Package Level 1 Units	100 piece
Package Level 2 Units	500 piece
Package Level 2 Width	5.25 in 133 mm
Package Level 2 Height	5.5 in 140 mm
Package Level 2 Depth / Length	15.25 in 387 mm

## Additional Information

Brand / Label	Ty-Rap
Bundle Diameter	0.138 to 3.07 in 3.5 to 78 mm
Color	Black
Lock Type	Stainless Steel Barb
Material	Nylon/Polyamide 6.6

Number of Batteries	0
Product Name	CABLE TIES
Product Type	Standard
Special Functions	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.
Surface Finishing	Untreated
Tensile Strength	50 lb 222 N
Thickness	0.055 in 1.4 mm
UPC	786210885131

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY5253MX
Instructions and Manuals	TY5253MX

### Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

### Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

