

## MPUUW ANALOG COUPLER COMPONENT

IN: 0..10 V - OUT: 0..10 V / 300 mA

INPUT: 0...10 V DC


OUTPUT: 0...10 V DC/300 mA

Screw terminals

This product is a processing component and must only be used by authorized manufacturers or people.

### [Link to Product](#)

#### Illustration



Regular voltage amplification

Product may differ from Image

#### Technical Data

Operating voltage	24 V DC $\pm 20\%$ , smoothed
-------------------	-------------------------------

Operating current	max. 300 mA
Tolerance	max. 0.5 %
Frequency	max. 1 kHz

**General data**

Mounting method	DIN-rail mountable (EN 60715)
Temperature range	0...+50 °C
Dimensions H × W × D	62×86×67.5 mm

**Voltage output signals**

Load	max. 300 mA
------	-------------

**Voltage inputs**

Input resistor	approx. 10 kOhm
----------------	-----------------

**Commercial data**

country of origin	CZ
customs tariff number	85437090
minimum order quantity	1