

## SVS VALVE PLUG FORM A 18MM FIELD-WIREABLE


110V/230V LED+RC M16x1.5

Form A (18 mm)  
110/230 V AC/DC with LED and RC  
metric



Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

### [Link to Product](#)

#### Illustration



stay connected



Height: 41 mm

Product may differ from Image

### Approvals



### Form

29121

### Technical Data

Operating voltage	110 V AC/DC $\pm 10\%$ and 230 V AC/DC $\pm 10\%$
Operating current per contact	max. 1 A
Max. power (W)	max. 50 W(VA)
Connection cross section	4 mm <sup>2</sup> single core, with ferrule end 1.5 mm <sup>2</sup>
Sealing range (cable diameter)	5...10 mm
Locking of ports	M3 (recommended torque 0.4 Nm)
Compression gland	M16 $\times$ 1.5 mm
Protection	IP65 inserted and tightened (EN 60529), with gland

### General data

Temperature range	-20...+60 °C
-------------------	--------------

### Commercial data

country of origin	CZ
customs tariff number	85369010
minimum order quantity	1