



RoHS ✓



The information/details in this datasheet merely contain general descriptions or performance factors which, when applied in an actual situation, do not always correspond with the described form, and may be amended by way of the further development of products. The desired performance factors shall only be binding if these are expressly agreed on conclusion of the contract.



Datasheet-No. 733-271-004 Type: **GMN 209-12**

EN Revision: 00 Created: 2011-08-05 aborkowi **Gasket**

Product description

Description	Flat gasket
Type	GMN 209-12 EPDM
Order No	733-271-004

Materials

Gasket(s)	EPDM, (brown) hardness: 55±5 Shore A (DIN 53505) 60±5 °M (DIN ISO 48 160) tracking: PTI 600 (DIN IEC 112)
-----------	--

Resistances

Gasket	UV-resistant ozone-resistant
--------	---------------------------------

Environmental conditions

Temperature range	-40°C to +150°C
-------------------	-----------------

product overview

Article-No.	Type
733-271-004	GMN 209-12 EPDM