




Reference Only

Revision	Date	Note
01	2007/12/05	Module Ass'y



Pin Assignment	
NO.	SYMBOL
1	VSS
2	VSL
3	VCC
4	VCOMH
5	VDD
6	BS1
7	BS2
8	CS#
9	RES#
10	D/C#
11	R/W#
12	E(RD#)
13	D0
14	D1
15	D2
16	D3
17	D4
18	D5
19	D6
20	D7
21	IREF
22	VCC
23	NC
24	VSS

- Specification**
1. Display: OLED (Yellow)
  2. Dot Matrix: 128x64
  3. Dot Size: 0.255x0.255mm
  4. Dot Pitch: 0.285x0.285mm
  5. Aperture Rate: 80%
  6. Active Area: 36.45x18.21mm
  7. IC: SSD1325



General Tolerance	
Length (mm)	Tolerance(mm)
0 ~ 8	±0.1
8 ~ 25	±0.2
25 ~ 50	±0.3

CONFIDENTIAL	
M.E.	E.E.
David Li	Kevan Huang

Scale	Unit	Sheet
1.5:1	mm	1/1
Module	Spec.	Approved
David Li	HC Lin	Strong Tsai

PROJECT CODE	
PART NAME	REVISION
PMO19401	01
PARTS NO.	REVISION
Module Ass'y	