

Clamping heads, round version

ORION®

Application:

Versatile in application, machining centres, all common axial force clamping systems on lathes and vices, measuring machines or pallet clamping.

Execution:

- High-strength rubber/metal connection
- High retention forces
- Corrosion protection coating

Art. no.	22001 054
Brand	ORION
Manufacturer Part Number	22001054
Size	32
Design	Without stem
Profile shape	Round with linear- and transverse grooves
Clamping diameter	31 mm
Length	44 mm
Min./max. clamping range diameter	11-32 mm
Gross Weight	0.280 kg
Product Group	2AO



EAN

4053625466702