

Horizontal quick-action clamp

With open clamping arm and horizontal base



Application:

For quick clamping of workpieces.

Version:

- Galvanised and passivated
- Ergonomic, oil-resistant handle with large hand rest and soft components.
- Case-hardened and lubricated bearing bushes

Delivery:

With thrust bolt and protective cap



Art. no.	26215 005
Size	0
Min./max. hole distance	11.5-15.5 mm
Hole distance 2	16 mm
Bore diameter	4.6 mm
Clamping height	14.5 mm
Retaining force	250 N
Max. tensile force	400 N
Height	23 mm
Length 2	79 mm
Thumbscrew size	M4 x 25 mm

EAN-Code

4020772093006