

Adjustable clamps

Angled



Application:

For clamping workpieces.

Version:

- With support screw and clamping screw
- Made from heat-treated steel
- Painted

Art. no.	26221 020
For table grooves according to DIN 650	12 mm
Suitable screw DIN 787	M12 x 100 mm
Min./max. clamping range	10-40 mm
Groove width	14 mm
Span iron length	100 mm
Span iron width	40 mm
Thread dimension	M12
Thread length	49 mm
Thickness	20 mm
Distance	21 mm
Length	40 mm



EAN-Code

4020772070274