

## Outside micrometer

With dial

Mitutoyo

### Application:

For measuring e.g. sheet thickness

### Version:

- Semi-gloss chrome-plated scale drum and sleeve
- Spherical anvil and flat spindle
- Friction coupling for consistent, repeatable measuring force

### Advantage:

- Easy-to-read display



<b>Art. no.</b>	<b>32016 479</b>
<b>Min./max. length measuring range</b>	0-25 mm
<b>Vernier scale</b>	0.01 mm
<b>Measuring surface diameter</b>	6.3 mm
<b>Bracket depth</b>	50 mm
<b>Spindle clamping</b>	Yes
<b>Error limit</b>	4 µm
<b>Display</b>	Analogue
<b>Calibration Group</b>	D
<b>Type</b>	With spherical anvil and flat spindle

### EAN-Code

4946368012032