

electronic pocket vernier calipers

angled internal/external measuring surfaces, knife-edge callipers

Mitutoyo

Application:

For carrying out internal measurements, measuring wall thickness in holes, carrying out measurements within a groove

Execution:

- Digimatic
- IP67
- AUTO OFF
- ABSOLUTE system for reliable measurement
- High-contrast display

Advantage:

- Suitable for special or difficult to reach measuring points

Delivery:

Delivered in box



| | |
|---|---|
| Art. no. | 32018 100 |
| Brand | MITUTOYO |
| Manufacturer Part Number | 573-752-20 |
| Min./max. length measuring range in inches | 0-6 in |
| Depth gauge rod | Without |
| IP protection class | IP 67 |
| With drive wheel | Yes |
| Error limit | 0.0015 in |
| Length of jaw | 40 mm |
| Design | Metric, Imperial |
| Digit height | 9 mm |
| Digit increment | 0.01 mm |
| Digit increment in inches | 0.0005 in |
| Type of locating | With locking screw |
| With mm / inch switching | Yes |
| Battery designation | 1,5 V SR44 |
| Number of rechargeable batteries/batteries | 1 PCS |
| Weight of rechargeable battery/battery | 0.002 kg |
| Battery voltage | 1.55 V |
| Type of rechargeable battery/battery | Silver oxide |
| Calibration Group | A |
| ISO | 13385-1 |
| Functions | Absolute function, With mm / inch switching, Points of knives, ABS function |
| Gross Weight | 0.520 kg |
| Product Group | 3MA |

EAN

4946368727042