

cordless angle drill DA332DZ

10.8 volt, without battery and without charger



Application:

Motor brake

Execution:

- very handy cordless angle drill
- just 63 mm from the upper edge of the gear unit to the tip of the drill chuck
- electronically controllable speed
- motor brake

Advantage:

- Very handy cordless angle drill

Delivery:

drill chuck key S10, PH bit 2x50, without battery, without charger.



Art. no.	71029 705
Model	DA332DZ
Battery included	No
Number of rechargeable batteries/batteries	0
Battery voltage	10.8 V/AC
Max. drilling diameter in wood	12 mm
Max. drilling diameter in steel	10 mm
Idle speed 1st gear min./max.	0-1100 rpm
Min./max. drill chuck span width	0.8-10 mm
Weight	1.3 kg
With working lights	Yes
With right/left-hand rotation	Yes
Length x width x height	332 x 68 x 86 mm
Product Group	Prod. Gr. 715

EAN

0088381849937