

ALFRA SPLIT HOLE PUNCHER TRICUT®

Ø in mm	Max. Material thickness in mm (S235)	Size Metric	Size PG	Size Inch		Size Conduit & Pipe Size	 Punches and dies, draw bolt with ball bearing	 Punches and dies	 matching draw bolt	 matching draw bolt with ball bearing	Prod.-No.			
12.5	1.5	M 12	7	1/2"	0.500	-	01674	01770	02022	01334				
15.2	2.0	-	9	-	0.598	-	01680	01771	02003	01339				
16.2	2.0	M 16	-	-	0.638	-	01683	01772						
18.6	2.0	-	11	-	0.732	-	01686	01773						
20.4	2.0	M 20	13	-	0.803	-	01689	01774						
22.5	2.0	-	16	7/8"	0.886	1/2"	01692	01775						
25.4	2.0	M 25	-	1"	1.000	-	01695	01776						
28.3	2.0	-	21	-	1.114	3/4"	01698	01777						
28.3	3.0	-	21	-	1.114	3/4"	01701	01778	02002	01340				
30.5	2.0	-	-	1-7/32"	1.201	-	01703	01779	02003	01339				
32.5	3.0	M 32	-	-	1.280	-	01708	01780	02002	01341				
34.6	3.0	-	-	1-11/32"	1.362	1"	01711	01788						
37.0	3.0	-	29	-	1.457	-	01713	01781						
40.5	3.0	M 40	-	-	1.594	-	01715	01782						
43.2	3.0	-	-	1-11/16"	1.701	1 1/4"	01718	01789						
47.0	3.0	-	36	-	1.850	-	01720	01783						
49.6	3.0	-	-	1-15/16"	1.953	1 1/2"	01723	01790						
50.5	3.0	M 50	-	-	1.988	-	01736	01784						
54.0	3.0	-	42	2-1/8"	2.126	-	01727	01785						
60.0	3.0	-	48	-	2.362	-	01729	01786						
61.5	3.0	-	-	2-3/8"	2.421	2"	01732	01791						
63.5	3.0	M 63	-	2-1/2"	2.500	-	01739	01787						