


Twin wire-end ferrules with plastic collars



Polypropylene insertion funnel

Heat resistant up to 105 °C

If required, the insertion funnel can also be manufactured from a low-flammability material

For conductors of 2 x 0.5-2 x 16 mm² (2 x AWG 20-2 x AWG6)

Material E-Cu, tin-plated

Dimensional tolerance acc. to DIN 46228, part 4

Weidmüller colour code

Packed loose




Type	Ø mm ²	AWG	L1	L2	D1	D2	S1	S2	Stripping length	Colour	Qty.	Order No.
H0,34/14 ZH TK	0.34	AWG 22	14.00				0.15			● Turquoise	500	1139070000
H0,5/14 ZH OR	0.5	AWG 20	14.00	8	1.4		0.15	0.3	11	● Orange	500	9037200000
H0,5/16 ZH OR	0.5	AWG 20	16.00	10	1.4		0.15	0.3	13	● Orange	500	9037210000
H0,5/18 ZH OR	0.5	AWG 20	18.00	12	1.4		0.15	0.3	15	● Orange	500	9037220000
H0,75/14 ZH W	0.75	AWG 18	14.00	8	1.7		0.15	0.3	11	○ White	500	9037230000
H0,75/16 ZH W	0.75	AWG 18	16.00	10	1.7		0.15	0.3	13	○ White	500	9037240000
H0,75/19S ZH W	0.75	AWG 18	19.00	12	1.7		0.15	0.3	21	○ White	500	9202820000
H0,75/24 ZH W	0.75	AWG 18	24.00	18	1.7		0.15	0.3	21	○ White	500	9037250000
H1,0/15 ZH GE	1	AWG 17	15.00	8	2		0.15	0.3	11	● Yellow	500	9037260000
H1,0/15S ZH GE	1	AWG 17	15.00	8	2.2		0.15	0.3	12	● Yellow	500	9018690000
H1,0/19 ZH GE	1	AWG 17	19.00	12	2		0.15	0.3	16	● Yellow	500	9037270000
H1,0/25 ZH GE	1	AWG 17	25.00	18	2		0.15	0.3	22	● Yellow	500	9037280000
H1,5/16 ZH R	1.5	AWG 16	16.00	8	2.2		0.15	0.3	11	● Red	500	9037290000
H1,5/20 ZH R	1.5	AWG 16	20.00	12	2.2		0.15	0.3	15	● Red	500	9037300000
H1,5/26 ZH R	1.5	AWG 16	26.00	18	2.2		0.15	0.3	21	● Red	100	9037310000
H2,5/19D ZH BL	2.5	AWG 14	19.00	10	2.8		0.15	0.4	13	● Blue	500	9037500000
H2,5/21D ZH BL	2.5	AWG 14	21.00	12	2.8		0.15	0.4	15	● Blue	100	9037510000
H2,5/27D ZH BL	2.5	AWG 14	27.00	18	2.8		0.15	0.4	21	● Blue	100	9037520000
H4,0/22D ZH GR	4	AWG 12	22.00	12	3.5		0.2	0.5	15	● Grey	100	9037530000
H4,0/28D ZH GR	4	AWG 12	28.00	18	3.5		0.2	0.5	21	● Grey	100	9037540000
H6,0/23 ZH SW	6	AWG 10	23.00	12	4.5		0.2	0.5	20	● Black	100	9037320000
H6,0/29 ZH SW	6	AWG 10	29.00	18	4.5		0.2	0.5	24	● Black	100	9037330000
H10,0/24 ZH EB	10	AWG 7	24.00	12	5.8		0.2	0.5	17	● Ivory	100	9037340000
H10,0/30 ZH EB	10	AWG 7	30.00	18	5.8		0.2	0.5	23	● Ivory	100	9037350000
H10,24S ZH EB	10	AWG 7	24.00	12	6.5		0.2	0.5	17	● Ivory	100	9018860000
H10,30S ZH EB	10	AWG 7	30.00	18	6.5		0.2	0.5	23	● Ivory	100	9018870000
H16,0/29 ZH GN	16	AWG 6	29.00	16	8.3		0.3	0.6	20	● Green	50	9037360000
H16,0/38 ZH GN	16	AWG 6	38.00	25	8.3		0.3	0.6	29	● Green	50	9037370000

Weidmüller colour code

In multi-pack bag



Type	Ø mm ²	AWG	L1	L2	D1	D2	S1	S2	Stripping length	Colour	Qty.	Order No.
H0,5/14 ZH	0.5	AWG 20	14.00	8	1.4		0.15	0.3	11	● Orange	500	9004440000
H0,75/14 ZH	0.75	AWG 18	14.00	8	1.7		0.15	0.3	11	○ White	500	9018510000
H0,75/16 ZH	0.75	AWG 18	16.00	10	1.7		0.15	0.3	13	○ White	500	9004900000
H1,0/15 ZH	1	AWG 17	15.00	8	2		0.15	0.3	12	● Yellow	500	9018530000
H1,0/15S ZH	1	AWG 17	15.00	8	2.2		0.15	0.3	12	● Yellow	500	9018650000
H1,0/19 ZH	1	AWG 17	19.00	12	2		0.15	0.3	16	● Yellow	500	9004910000
H1,5/16 ZH	1.5	AWG 16	16.00	8	2.2		0.15	0.3	11	● Red	500	9004410000
H2,5/19D ZH	2.5	AWG 14	19.00	10	2.8		0.15	0.4	13	● Blue	250	9004430000
H1,5/20 ZH	1.5	AWG 16	20.00	12	2.2		0.15	0.3	15	● Red	500	9004920000
H2,5/21D ZH	2.5	AWG 14	21.00	12	2.8		0.15	0.4	15	● Blue	250	9004740000
H4/22D ZH G	4	AWG 12	22.00	12	3.5		0.2	0.5	15	● Grey	100	9004730000
H6,0/23 ZH	6	AWG 10	23.00	12	4.5		0.2	0.5	20	● Black	100	9004930000
H10,0/24 ZH	10	AWG 7	24.00	12	5.8		0.2	0.5	17	● Ivory	100	9004940000



- Polypropylene conical entry funnel
- Heat-resistant up to 105°C
- The entry funnel can also be manufactured from a non-flammable material on request

For conductors of 2 x 0.5-2 x 16 mm² (2 x AWG 20-2 x AWG6)

Material E-Cu, electro-galvanised

Dimensional tolerance acc. to DIN 46228 Part 4

DIN colour code

Packed loose



Type	Ø mm ²	AWG	L1	L2	D1	D2	S1	S2	Stripping length	Colour	Qty.	Order No.
H0,5/14D ZH W	0.5	AWG 20	14.00	8	1.4		0.15	0.3	11	○ White	500	9037380000
H0,5/16D ZH W	0.5	AWG 20	16.00	10	1.4		0.15	0.3	13	○ White	500	9037390000
H0,5/18D ZH W	0.5	AWG 20	18.00	12	1.4		0.15	0.3	15	○ White	500	9037400000
H0,75/14D ZH GR	0.75	AWG 18	14.00	8	1.7		0.15	0.3	11	● Grey	500	9037410000
H0,75/16D ZH GR	0.75	AWG 18	16.00	10	1.7		0.15	0.3	13	● Grey	500	9037420000
H0,75/19DS ZH GR	0.75	AWG 18	19.00	12	1.7		0.15	0.3	21	● Grey	500	9202830000
H0,75/24D ZH GR	0.75	AWG 18	24.00	18	1.7		0.15	0.3	21	● Grey	500	9037430000
H1,0/15D ZH R	1	AWG 17	15.00	8	2		0.15	0.3	11	● Red	500	9037440000
H1,0/19D ZH R	1	AWG 17	19.00	12	2		0.15	0.3	16	● Red	500	9037450000
H1,0/22DS R ZH	1	AWG 17	22.00		2		0.15	0.3	21	● Red	500	9036330000
H1,0/25D ZH R	1	AWG 17	25.00	18	2		0.15	0.3	22	● Red	500	9037460000
H1,5/16D ZH SW	1.5	AWG 16	16.00	8	2.2		0.15	0.3	11	● Black	500	9037470000
H1,5/20D ZH SW	1.5	AWG 16	20.00	12	2.2		0.15	0.3	15	● Black	500	9037480000
H1,5/26D ZH SW	1.5	AWG 16	25.00	18	2.2		0.15	0.3	21	● Black	100	9037490000
H2,5/19D ZH BL	2.5	AWG 14	19.00	10	2.8		0.15	0.4	13	● Blue	500	9037500000
H2,5/21D ZH BL	2.5	AWG 14	21.00	12	2.8		0.15	0.4	15	● Blue	100	9037510000
H2,5/27D ZH BL	2.5	AWG 14	27.00	18	2.8		0.15	0.4	21	● Blue	100	9037520000
H4,0/22D ZH GR	4	AWG 12	22.00	12	3.5		0.2	0.5	15	● Grey	100	9037530000
H6,0/23D ZH GE	6	AWG 10	23.00	12	4.5		0.2	0.5	20	● Yellow	100	9037550000
H4,0/28D ZH GR	4	AWG 12	28.00	18	3.5		0.2	0.5	21	● Grey	100	9037540000
H6,0/29D ZH GE	6	AWG 10	29.00	18	4.5		0.2	0.5	24	● Yellow	100	9037560000
H10,0/24D ZH R	10	AWG 7	24.00	12	5.8		0.2	0.5	17	● Red	100	9037570000
H10,0/24DS ZH R	10	AWG 7	24.00	12	6.5		0.2	0.5	17	● Red	100	9018880000
H10,0/30D ZH R	10	AWG 7	30.00	18	5.8		0.2	0.5	23	● Red	100	9037580000
H10/30DS ZH R	10	AWG 7	30.00	18	6.5		0.2	0.5	23	● Red	100	9018890000
H16,0/29D ZH BL	16	AWG 6	29.00	16	8.3		0.3	0.6	20	● Blue	50	9037590000
H16,0/38D ZH BL	16	AWG 6	38.00	25	8.3		0.3	0.6	29	● Blue	50	9037600000


DIN colour code

In multi-pack bag



Type	Ø mm ²	AWG	L1	L2	D1	D2	S1	S2	Stripping length	Colour	Qty.	Order No.
H0,5/14D ZH	0.5	AWG 20	14.00	8	1.4		0.15	0.3	11	○ White	500	9004780000
H0,75/14D Z	0.75	AWG 18	14.00	8	1.7		0.15	0.3	11	● Grey	500	9018520000
H1,0/15D ZH	1	AWG 17	15.00	8	2.2		0.15	0.3	12	● Red	500	9018540000
H1,0/19D ZH	1	AWG 17	19.00	12	2		0.15	0.3	16	● Red	500	9004760000
H0,75/16D Z	0.75	AWG 18	16.00	10	1.7		0.15	0.3	13	● Grey	500	9004770000
H1,5/16D ZH	1.5	AWG 16	16.00	8	2.2		0.15	0.3	11	● Black	500	9004420000
H1,5/20D SW	1.5	AWG 16	20.00	12	2.2		0.15	0.3	15	● Black	500	9004750000
H2,5/19D ZH	2.5	AWG 14	19.00	10	2.8		0.15	0.4	13	● Blue	250	9004430000
H2,5/21D ZH	2.5	AWG 14	21.00	12	2.8		0.15	0.4	15	● Blue	250	9004740000
H4/22D ZH G	4	AWG 12	22.00	12	3.5		0.2	0.5	15	● Grey	100	9004730000
H6,0/23D ZH	6	AWG 10	23.00	12	4.5		0.2	0.5	20	● Yellow	100	9004720000
H10,0/26D R	10	AWG 7	26.00	12	5.8		0.2	0.5	17	● Red	100	9004710000

Twin wire-end ferrules with plastic collars



- Polypropylene conical entry funnel
- Heat-resistant up to 105°C
- The entry funnel can also be manufactured from a non-flammable material on request

For conductors of 2 x 0.5-2 x 16 mm² (2 x AWG 20-2 x AWG6)

Material E-Cu, electro-galvanised

Dimensional tolerance acc. to DIN 46228 Part 4

Other colour code

Packed loose



Type	Ø mm ²	AWG	L1	L2	D1	D2	S1	S2	Stripping length	Colour	Qty.	Order No.
H0,5/14 ZH OR	0.5	AWG 20	14.00	8	1.4		0.15	0.3	11	● Orange	500	9037200000
H0,5/16 ZH OR	0.5	AWG 20	16.00	10	1.4		0.15	0.3	13	● Orange	500	9037210000
H0,75/14T ZH HBL	0.75	AWG 18	14.00	8	1.7		0.15	0.3	11	● Light Blue	500	9037610000
H0,5/18 ZH OR	0.5	AWG 20	18.00	12	1.4		0.15	0.3	15	● Orange	500	9037220000
H0,75/16T ZH HBL	0.75	AWG 18	16.00	10	1.7		0.15	0.3	13	● Light Blue	500	9037620000
H0,75/19TS ZH HBL	0.75	AWG 18	19.00	12	1.7		0.15	0.3	21	● Light Blue	500	9202840000
H0,75/24T ZH HBL	0.75	AWG 18	24.00	18	1.7		0.15	0.3	21	● Light Blue	500	9037630000
H1,0/15D ZH R	1	AWG 17	15.00	8	2		0.15	0.3	11	● Red	500	9037440000
H1,0/19D ZH R	1	AWG 17	19.00	12	2		0.15	0.3	16	● Red	500	9037450000
H1,0/25D ZH R	1	AWG 17	25.00	18	2		0.15	0.3	22	● Red	500	9037460000
H1,5/16D ZH SW	1.5	AWG 16	16.00	8	2.2		0.15	0.3	11	● Black	500	9037470000
H1,5/20D ZH SW	1.5	AWG 16	20.00	12	2.2		0.15	0.3	15	● Black	500	9037480000
H1,5/26D ZH SW	1.5	AWG 16	25.00	18	2.2		0.15	0.3	21	● Black	100	9037490000
H2,5/19T ZH GR	2.5	AWG 14	19.00	10	2.8		0.15	0.4	13	● Grey	500	9037640000
H2,5/21T ZH GR	2.5	AWG 14	21.00	12	2.8		0.15	0.4	15	● Grey	100	9037650000
H2,5/27T ZH GR	2.5	AWG 14	27.00	18	2.8		0.15	0.4	21	● Grey	100	9037660000
H4,0/22T ZH OR	4	AWG 12	22.00	12	3.5		0.2	0.5	15	● Orange	100	9037670000
H4,0/28T ZH OR	4	AWG 12	28.00	18	3.5		0.2	0.5	21	● Orange	100	9037680000
H6,0/23T ZH GN	6	AWG 10	23.00	12	4.5		0.2	0.5	20	● Green	100	9037690000
H6,0/29T ZH GN	6	AWG 10	29.00	18	4.5		0.2	0.5	24	● Green	100	9037700000
H10,0/24T ZH BR	10	AWG 7	24.00	12	5.8		0.2	0.5	17	● Brown	100	9037710000
H10,0/30T ZH BR	10	AWG 7	30.00	18	5.8		0.2	0.5	23	● Brown	100	9037720000
H16,0/29T ZH W	16	AWG 6	29.00	16	8.3		0.3	0.6	20	○ White	50	9037730000
H16,0/38T ZH W	16	AWG 6	38.00	25	8.3		0.3	0.6	29	○ White	50	9037740000

Other colour code

In multi-pack bag



Type	Ø mm ²	AWG	L1	L2	D1	D2	S1	S2	Stripping length	Colour	Qty.	Order No.
H0,75/16T Z	0.75	AWG 18	16.00	10	1.7		0.15	0.3	13	● Light Blue	500	9005140000
H1,0/15D ZH	1	AWG 17	15.00	8	2.2		0.15	0.3	12	● Red	500	9018540000
H1,0/19D ZH	1	AWG 17	19.00	12	2		0.15	0.3	16	● Red	500	9004760000
H1,5/16D ZH	1.5	AWG 16	16.00	8	2.2		0.15	0.3	11	● Black	500	9004420000
H1,5/20D SW	1.5	AWG 16	20.00	12	2.2		0.15	0.3	15	● Black	500	9004750000
H2,5/19T ZH	2.5	AWG 14	19.00	10	2.8		0.15	0.4	13	● Grey	250	9018580000
H2,5/21 ZH	2.5	AWG 14	21.00	12	2.8		0.15	0.4	15	● Grey	250	9005150000
H4,0/22T ZH	4	AWG 12	2.00	12	3.5		0.2	0.5	15	● Orange	100	9018590000
H6,0/23T ZH	6	AWG 10	23.00	12	4.5		0.2	0.5	20	● Green	100	9005160000
H10,0/26T Z	10	AWG 7	26.00	12	5.8		0.2	0.5	17	● Brown	100	9005170000