

MILAN S.r.l. a socio unico

Head Office – Export department:
 Viale Europa, 74
 20090 Cusago (MI) Italy
 T. +39 02 9039.4556-4158
 F. +39 02 9039.4551
 www.taskercables.com

Ufficio Commerciale e Centro Distribuzione
 Viale Europa 72 Strada F12
 20090 Cusago (MI) Italy
 T. +39 02 9039.0037-0059
 F. +39 02 9039.0049
 www.tasker.it

Technical Datasheet



tasker® C128 – 2x0,35 mm² Low Capacity Balanced Microphone Cable




CATEGORY Balanced Microphone Cable (See Audio Catalogue)

- A:** Soft PVC Sheath – Available in different color.
Outer cable Diam. Ø 6,30 (±0,20) mm.
- B:** Braided Shielding O.F.C. tinned copper covering 90%.
- C:** The cores will be stranded in a pair with textile waste filler between conductors and wrapped with not woven polyester based tape.
- D:** Transparent Cores Insulation with compact PE. Diam. Ø 1,70 mm (±0,20) mm.
- E:** One conductor in O.F.C. red copper and one in O.F.C. tinned copper – formation 11x0,20 mm. Nom. Cross section 2x0,35 mm².

MARKING tasker® C128 2x0,35 mm² O.F.C. Low Capacitance Supreme Microphone Cable Made in Italy.

CUSTOM This product is also available in L.S.Z.H. polymer, PE, PUR, with or without Steel Armor.

Attenuation Test – Start 9 KHz – Stop 25 KHz



Cable Properties

Conductor Resistance	60 Ω/Km ± 5%
Capacity Core/Core	55 pF/mt
Capacity Core/Shield	92 pF/mt
Max Rated Voltage	49 V
Operative Temperature	-15/+70°C ± 10%

USE	X	Indoor	Interno Edificio
Impiego	X	Outdoor Limited	Esterno Limitato
		Outdoor Direct Burial	Esterno Interrato

INSTALLATION	X	Fixed	Fissa
Posa	X	Flexible Limited	Flessibilità limitata
	X	Dynamic (Drag Chain)	Mobile in Catena
		Dynamic (Torsion)	Mobile in Torsione

INFORMATION	X	RoHS2 Compliant
Informazioni	X	Ver. B/ 21.10.2015