



Modular terminal blocks - CLIPLINE complete


PT push-in connection terminal blocks



2.5 (4) mm², 30 A, feed-through terminal block



4 (6) mm², 38 A, feed-through terminal block



6 (10) mm², 52 A, feed-through terminal block

Ex:

 PTB 09ATEX1111U / IECEx PTB 10.0021U

Ex:

 PTB 09ATEX1112U / IECEx PTB 10.0046U

Technical data			
Width	Length	Height NS 35/7,5	
5.2	48.5	36.5	
I_{max} [A]	U_{max} [V]	max. Ø [mm ²]	AWG
30	800	0.14 - 4	26 - 12
IEC 60947-7-1			
IEC	UL/CUL	CSA	IEC/EN 60079-7
800	600	600	550
24 / 2.5	20 / -	20 / -	28
2.5	-	-	2.5
26 - 12	26-12	26-12	26 - 12
solid	stranded	Ferrule	
		Without / with plastic sleeve	
0.14 - 4	0.14 - 2.5	0.14 - 2.5	0.14 - 2.5
		0.5	
0.34 - 4	-	0.34 - 2.5	0.34 - 2.5
10			
PA			
V0			

Technical data			
Width	Length	Height NS 35/7,5	
6.2	56	36.5	
I_{max} [A]	U_{max} [V]	max. Ø [mm ²]	AWG
38	800	0.2 - 6	24 - 10
IEC 60947-7-1			
IEC	UL/CUL	CSA	IEC/EN 60079-7
800	600	600	550
32 / 4	30 / -	30 / -	27
4	-	-	4
24 - 10	24-10	24-10	24 - 10
solid	stranded	Ferrule	
		Without / with plastic sleeve	
0.2 - 6	0.2 - 4	0.25 - 4	0.25 - 4
		0.5 - 1	
0.5 - 6	-	0.5 - 4	0.5 - 4
12			
PA			
V0			

Technical data			
Width	Length	Height NS 35/7,5	
8.2	57.7	43.5	
I_{max} [A]	U_{max} [V]	max. Ø [mm ²]	AWG
52	1000	0.5 - 10	20 - 8
IEC 60947-7-1			
IEC	UL/CUL	CSA	IEC/EN 60079-7
1000	600	600	-
41 / 6	40 / -	40	-
6	-	-	-
20 - 8	20-8	20-8	-
solid	stranded	Ferrule	
		Without / with plastic sleeve	
0.5 - 10	0.5 - 6	0.5 - 6	0.5 - 6
		0.5 - 1.5	
1 - 10	-	1 - 6	1 - 6
12			
PA			
V0			

Ordering data			
Type	I_{max}	Order No.	Pcs. / Pkt.
PT 2,5		3209510	50
PT 2,5 BU		3209523	50

Ordering data			
Type	I_{max}	Order No.	Pcs. / Pkt.
PT 4		3211757	50
PT 4 BU		3211760	50

Ordering data			
Type	I_{max}	Order No.	Pcs. / Pkt.
PT 6		3211813	50
PT 6 BU		3211819	50

Accessories ¹⁾			
D-ST 2,5		3030417	50
D-ST 2,5-0,8 OG		3030511	50
ISH 2,5/0,2		3002843	50
ISH 2,5/0,5		3002856	50
ISH 2,5/1,0		3002869	50
FBS 2-5	24 A	3030161	50
FBS 3-5	24 A	3030174	50
FBS 4-5	24 A	3030187	50
FBS 5-5	24 A	3030190	50
FBS 10-5	24 A	3030213	10
FBS 20-5	24 A	3030226	10
ATP-ST 4		3030721	50
PAI-4-N GY		3032871	10
MPS-MT		0201744	10
MPS-IH RD		0201676	10
PS-5		3030983	10
SZF 1-0,6X3,5		1204517	10

Accessories ¹⁾			
D-ST 4		3030420	50
ISH 4/0,5		3002885	50
ISH 4/1,0		3002898	50
FBS 2-6	32 A	3030336	50
FBS 3-6	32 A	3030242	50
FBS 4-6	32 A	3030255	50
FBS 5-6	32 A	3030349	50
FBS 10-6	32 A	3030271	10
FBS 20-6	32 A	3030365	10
RB ST (2,5/4)-1,5/S		3214356	10
ATP-ST 4		3030721	50
PAI-4-N GY		3032871	10
MPS-MT		0201744	10
MPS-IH RD		0201676	10
PS-6		3030996	10
SZF 1-0,6X3,5		1204517	10

Accessories ¹⁾			
D-PT 6		3212044	50
FBS 2-8	24 A	3030284	10
FBS 3-8	24 A	3030297	10
FBS 4-8	24 A	3030307	10
FBS 5-8	24 A	3030310	10
FBS 10-8	24 A	3030323	10
RB ST 6-1,5/S		3213250	10
ATP-ST 6		3024481	50
PAI-4-N GY		3032871	10
MPS-MT		0201744	10
MPS-IH RD		0201676	10
PS-8		3031005	10
SZF 2-0,8X4,0		1204520	10

UC-TM 5, UCT-TM 5 or ZB 5
 (see Catalog 5)
 UC-TMF 5, UCT-TMF 5 or ZBF 5
 (see Catalog 5)

UC-TM 6, UCT-TM 6 or ZB 6
 (see Catalog 5)
 UC-TMF 6, UCT-TMF 6 or ZBF 6
 (see Catalog 5)

UC-TM 8, UCT-TM 8 or ZB 8
 (see Catalog 5)
 UC-TMF 8, UCT-TMF 8 or ZBF 8
 (see Catalog 5)