


# EBC004



## Splitter box

ZDO4H059MSS0000-00STAK190MSS



### Application

Special feature	Free from silicone; Gold-plated contacts
Free from silicone	yes

### Electrical data

Operating voltage	[V]	10...30 DC; ("supply class 2" to cULus)
Max. current load per module/slot	[A]	4
Max. current load total	[A]	10

### Outputs

Electrical design	PNP
-------------------	-----

# EBC004



## Splitter box

ZDO4H059MSS0000-00STAK190MSS


Operating conditions		
Ambient temperature [°C]		-25...80
Protection		IP 67; ("enclosure type 1" according to cULus)
Mechanical data		
Weight [g]		226
Dimensions [mm]		33 x 60 x 118.2
Materials		PA
Number of ports splitter box		4
Connector type		M12
Displays / operating elements		
Display	switching status	8 x LED, yellow
	operation	1 x LED, green
Accessories		
Accessories (supplied)		Protective caps: 2 labels: 4
Remarks		
Pack quantity		1 pcs.
Electrical connection - Connection		
Connector: 1 x M23; Moulded body: PA; Contacts: gold-plated; Tightening torque: 0.8...1.5 Nm		



## Splitter box

ZDO4H059MSS0000-00STAK190MSS

### Connection



### Electrical connection - slot

Connector: 4 x M12; Moulded body: PA; Contacts: gold-plated; Tightening torque: 0.8...1.5 Nm

