

PTC HEATING BLAST CS030 AC 120V, 1200W



Model		
product brand name		SIVACON
General technical data		
Active power consumption / Rated value	W	1 200
Volume flow rate / free-blowing	m ³ /h	160
Voltage		
Inrush current / typical	A	16
Protection class		
Protection class IP		IP20
Main circuit		
Operating voltage		
• with AC / at 50 Hz / Rated value / maximum	V	120
• with AC / at 60 Hz / Rated value / minimum	V	120
Operating current / of the slow-blow fuse link	A	10
Product details		
Product component		
• blower		Yes
• Thermostat		Yes
Connections		
Tightening torque / with screw-type terminals / maximum	N·m	0.8
Mechanical Design		

Height	mm	168
Width	mm	145
Depth	mm	120
Material / of the enclosure		plastic

Environmental conditions

Relative humidity / Reference value	%	90
-------------------------------------	---	----

Certificates

Equipment marking		
<ul style="list-style-type: none"> • acc. to DIN EN 61346-2 • acc. to DIN EN 81346-2 		R E

General Product Approval



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8MR21512A>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/8MR21512A/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=8MR21512A

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>



last modified:

11.03.2015