



STI-Taps (Second Lead)
for Wire-Thread-Inserts Tolerance 2B

Maschi STI
per inserti riportati dopo tolleranza 2B



Form D HSS-G Tol. 3B UNC/UNF

Nominal Diameter D	B	L1	L2	D2	☒	Art.-No.
UNC/NC						
No. 2 x 56	2.8	48.0	10.0	3.15	2.5	03100
No. 4 x 40	3.7	53.0	13.0	4.0	3.15	03101
No. 5 x 40	4.0	53.0	13.0	4.0	3.15	03102
No. 6 x 32	4.5	58.0	16.0	5.0	4.00	03103
No. 8 x 32	5.2	62.0	17.0	5.6	4.50	03104
No. 10 x 24	6.2	66.0	19.0	6.3	5.00	03105
No. 12 x 24	6.9	66.0	19.0	7.1	5.60	03106
1/4 x 20	8.0	72.0	22.0	8.0	6.30	03107
5/16 x 18	9.8	80.0	24.0	10.0	8.00	03108
3/8 x 16	11.6	85.0	25.0	8.0	6.30	03109
7/16 x 14	13.5	95.0	30.0	11.2	9.00	03110
1/2 x 13	15.2	102.0	32.0	12.5	10.00	03111
9/16 x 12	17.0	112.0	37.0	14.0	11.20	03112
5/8 x 11	18.9	112.0	37.0	14.0	11.20	03113
3/4 x 10	22.4	118.0	38.0	16.0	12.50	03114
7/8 x 9	25.9	130.0	45.0	18.0	14.00	03115
1" x 8	29.5	138.0	48.0	20.0	16.00	03116
UNF/NF						
No. 4 x 48	3.5	53.0	13.0	4.0	3.15	03151
No. 6 x 40	4.3	53.0	13.0	4.5	3.55	03152
No. 8 x 36	5.1	62.0	17.0	5.6	4.50	03153
No. 10 x 32	5.9	66.0	19.0	6.3	5.00	03154
1/4 x 28	7.5	69.0	19.0	8.0	6.30	03155
5/16 x 24	9.3	76.0	20.0	10.0	8.00	03156
3/8 x 24	10.9	82.0	22.0	8.0	6.30	03157
7/16 x 20	12.8	84.0	24.0	9.0	7.10	03158
1/2 x 20	14.4	90.0	25.0	11.2	9.00	03159
9/16 x 18	16.1	104.0	29.0	12.5	10.00	03160
5/8 x 18	17.7	104.0	29.0	14.0	11.20	03161
3/4 x 16	21.1	104.0	29.0	14.0	11.20	03162
7/8 x 14	24.6	120.0	35.0	18.0	14.00	03163
1" x 12	28.2	127.0	37.0	20.0	16.00	03164
1" x 14	27.8	127.0	37.0	20.0	16.00	03165

