


ART.: 8607891363400

FL SQUARE 600 IL OP



Art.: 8607891363400, FL SQUARE IL, Direct, 33W, 4000K, Driver static, 596mm, Symmetrical, > 75°, White, Lay-in LED luminaire for indoors, consisting of: Die-cast aluminium housing, powder-coated / LED Sidelight-Technology and light orienting plastic optic for a homogenous light distribution over the entire area of the cover / Colour rendering index Ra > 80 / Colour tolerance according to MacAdam = 3 SDCM / Suitable for lattice and coffered ceilings / Complete with electric converter / UGR <19 for all luminosities / Protection class IP43 (for light emission surface for installation in closed ceilings) / Recessed luminaire can only be used for cut ceilings with separately available installation frames / Separate accessory allows the lights to be used as a suspended, surface mounted or recessed luminaires

Connected load	33 W
Luminous flux	3920 lm
Efficiency	119 lm/W
Colour temperature	4000K
Colour rendering (CRI)	80
IP class	20
Nominal voltage	220 – 240 V
Colour	WH-RAL9016
UGR	≤ 22

