

Click Flat Diffusers

Cover C9 click 1m opal
0022616



Product features

- A click diffuser made of acrylic thermoplastic (PMMA). Operating temperature: -20 - 70 [°C]. IK rating: 08. UV resistant. Fire hazard certificate according to IEC 60695-2-11. Compatible with the following profiles: Profile deep wide surface 30 CDE-9/T (0022590), Profile shallow wide surface 30 CDE-9/T (0022591). Transparency level 75%.



PRODUCT OVERVIEW

Product name	Cover C9 click 1m opal
Technology	Accessory
Housing	Aluminium
General application	Retail
ETIM Class	EC002557
E-number FI	4278035
Warranty	3 years
Housing colour	Silver
Product EAN number	5410288226163

DATA TABLE

General data

Product name	Cover C9 click 1m opal
Technology	Accessory
Housing	Aluminium
General application	Retail
ETIM Class	EC002557
E-number FI	4278035
Warranty	3 years

Physical data

Housing colour	Silver
Diffuser finish	Opal
Nominal Product Length (mm)	1000
Nominal Product Width (mm)	30
Nominal Product Height (mm)	4.3
Weight (kg)	0.02

Packaging

Single packaging type	Carton
Product EAN number	5410288226163

Click Flat Diffusers

Cover C9 click 1m opal

0022616

Packaging single length / height (cm)	100.0
Packaging single width (cm)	3.0
Packaging single depth (cm)	2.0
DUN14 (outer)	05410288226163
Units per outer package	100
Packaging outer length / height (cm)	205.0
Packaging outer width (cm)	16.0
Packaging outer depth (cm)	16.0

TECHNICAL DRAWINGS

