

Tipping containers, manual tipping - mobile container with Totalstop brakes

Carrying capacity: up to 800 kg

fetra
Transportgeräte

Application:

For the collection and disposal of all types of bulk goods and solid materials with floor-level emptying option.

Version:

- Skip with sliding handle
- Robust sheet steel construction, double-folded top rim, double-folded dumping edge
- 2 steering and 2 fixed castors, 200 x 40 mm TPE wheels, hubs with grooved ball bearings, Totalstop braking system
- No link chain slide guard (see no. 50266034)

Advantage:

- Totalstop brake system for ideal locking of container for tipping
- With floor-level emptying option



| | |
|--|--------------------------|
| Art. no. | 50266 016 |
| Volume | 0.8 m ³ |
| Length | 1458 mm |
| Width | 1105 mm |
| Tipper edge height | 843 mm |
| Height | 1099 mm |
| Fork pocket clearance | 577 mm |
| Fork pocket size (W x H) | 194 x 72 mm |
| Number of wheels | 4 |
| With drain valve | No |
| With stacker seat tilt function | No |
| With wheel lock | Totalstop |
| With perforated sheet | No |
| Load-carrying capacity | 800 kg |
| Surface | Powder-coated |
| Colour | Anthracite grey RAL 7016 |

EAN-Code

4017976247007