

# Deburring insert



## Application:

For quick and easy deburring in manual mode or for electric drive with 10-mm clamping range and maximum rotational speed 300 rpm, this solid all-metal tool comprises a deburring insert with four specially ground deburring blades and a driver. Suitable for exterior and interior deburring of stainless steel, steel, copper, brass, aluminium and plastic pipes 10-42 mm in diameter. To change between exterior and interior deburring, simply rotate the insert.

Art. no.	78233 020
Brand	REMS
Manufacturer Part Number	113810 R
Model	Deburring insert as replacement
Min./max. workpiece diameter	10-42 mm
Max. rotation speed	300 rpm
Gross Weight	0.500 kg
Product Group	783



## EAN

4039976021029

