

## Deburring insert



### Application:

For quick and easy deburring in manual mode or for electric drive with 10-mm clamping range and maximum rotational speed 300 rpm, this solid all-metal tool comprises a deburring insert with four specially ground deburring blades and a driver. Suitable for exterior and interior deburring of stainless steel, steel, copper, brass, aluminium and plastic pipes 10-42 mm in diameter. To change between exterior and interior deburring, simply rotate the insert.

<b>Art. no.</b>	<b>78233 020</b>
<b>Model</b>	Deburring insert as replacement
<b>Min./max. workpiece diameter</b>	10-42 mm
<b>Max. rotation speed</b>	300 rpm

### EAN-Code

4039976021029

