

Features

Photocrescenta lamps have an internal white coating, which emits diffused, very uniform light at high luminous output.

Max. permissible base temperature is 250 °C. The burning position of Photocrescenta lamps is universal.

Application


• Black-and-white photographic enlargers.




FP


| ⊏ | В |
|---|---|


| Туре | Lamp wattage W | Lamp voltage V | Cap/ base | Finish | ANSI code | LIF code | Lumen output Im | Colour temperature | Lamp life 50% h | Ordering number |
|-----------|----------------------|----------------------|--------------|----------------|-----------|----------|-----------------------|--------------------|--------------------------|--------------------|
| PF603E/51 | 75 | 230 | E27 | INTERNAL WHITE | - | P3/3 | 1100 | 2800 | 100 | 9205 311 44200 |
| PF603E/51 | 75 | 240 | E27 | INTERNAL WHITE | - | P3/3 | 1100 | 2800 | 100 | 9205 311 45500 |
| PF605E/51 | 150 | 230 | E27 | INTERNAL WHITE | - | P3/4 | 2500 | 2800 | 100 | 9205 321 44200 |
| PF605E/51 | 150 | 240 | E27 | INTERNAL WHITE | - | P3/4 | 2500 | 2800 | 100 | 9205 321 45500 |
| PF607E/51 | 250 | 230 | E27 | INTERNAL WHITE | - | P3/6 | 6500 | 3000 | 3 | 9205 326 44200 |
| PF607E/51 | 250 | 240 | E27 | INTERNAL WHITE | - | P3/6 | 6500 | 3000 | 3 | 9205 326 45500 |





Α В nom. max. 60.0 107.5





Burning position