

# Web panel - WP 6070-WVPS



1290800

<https://www.phoenixcontact.com/gb/products/1290800>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

IP66 Touch panel with 7.0-inch widescreen (16:9) VGA, PCAP display, Software: Qt Browser



## Your advantages

- Easy startup – just enter the IP and URL
- Flexible, thanks to open web standard and free choice of web server and visualization software
- No security updates are required for JAVA or Flash plug-ins thanks to HTML5
- Ideal for use with PLCnext Engineer or CODESYS
- Embedded Linux operating system
- Visualization of self-programmed JavaScript applications possible

## Commercial Data

Item number	1290800
Packing unit	1 pc
Minimum order quantity	1 pc
Sales Key	DRCADF
Product Key	DRCADF
GTIN	4063151522568
Weight per Piece (including packing)	2,260 g
Weight per Piece (excluding packing)	2,100 g
Customs tariff number	84714100
Country of origin	TW

## Technical Data

### Product properties

Product type	Operator panel
--------------	----------------

### Computer data

Processor	Arm® Cortex®-A53, 1.6 GHz
Operating system	Yocto/Linux
Data storage	Flash eMMC, 8 GB
Slots	1x microSD

### Display

Display type	17.8 cm/7" TFT
Screen resolution	800 x 480 Pixel(s) (WVGA)
Touch technology	projective-capacitive (PCAP)
Display lighting type	LED
Brightness	500 cd/m² typical (adjustable)
MTBF	50000 h
Color spectrum	16.7 million colors
Reading angle left	89 °
Reading angle right	89 °
Reading angle top	89 °
Reading angle bottom	89 °

### Software

User software	QT browser
---------------	------------

### System requirements

Runtime system	Qt Browser
----------------	------------

### Interfaces

Interfaces	2x USB Host 2.0, 1x USB Type C 3.0 1x COM (RS-232/422/485)
Optional interfaces	Without optional interface
Network	1x Ethernet (10/100/1000 Mbps), RJ45
Bus system	without

### Electrical properties

#### Supply

Supply voltage	24 V DC
Supply voltage range	18 V ... 32 V
Power supply unit	24 V DC ±20 %

#### Real-time clock

Realtime clock	Integrated (battery backup)
----------------	-----------------------------

1290800

<https://www.phoenixcontact.com/gb/products/1290800>

## Mounting

Mounting type	Front installation
---------------	--------------------

## Material specifications

Material front plate	Aluminum (natural anodized)
Housing material	Aluminum cast alloy, powder-coated

## Ambient conditions

Degree of protection	IP66 (front), IP20 (back)
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 60 °C
Permissible humidity (operation)	5 % ... 85 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 85 % (non-condensing)
Vibration (operation)	1g

## Dimensions

### External dimensions

Width / Height / Depth	202 mm / 146 mm / 51 mm (Dimensions of the front plate)
------------------------	---

### Installation dimensions

Width / Height / Installation depth	195 mm / 139 mm / (Installation cutout)
-------------------------------------	---

# Web panel - WP 6070-WVPS



1290800

<https://www.phoenixcontact.com/gb/products/1290800>

## Approvals



**EAC**

Approval ID: RU C-DE.A\*08.B01708



**IECEE CB Scheme**

Approval ID: US-39088-UL



**UL Listed**

Approval ID: FILE E 238705



**cUL Listed**

Approval ID: FILE E 238705

**cULus Listed**

1290800

<https://www.phoenixcontact.com/gb/products/1290800>

## Classifications

### ECLASS

ECLASS-9.0	27330201
ECLASS-10.0.1	27330201
ECLASS-11.0	27330201

### ETIM

ETIM 8.0	EC001412
----------	----------

### UNSPSC

UNSPSC 21.0	43211900
-------------	----------

# Web panel - WP 6070-WVPS

1290800

<https://www.phoenixcontact.com/gb/products/1290800>



## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
	1,2-dimethoxyethane,ethylene glycol dimethyl ether (EGDME) 110-71-4

# Web panel - WP 6070-WVPS

1290800

<https://www.phoenixcontact.com/gb/products/1290800>



## Accessories

### Battery

Battery - TP/WP 6000 RTC BATTERY KIT - 1289761

<https://www.phoenixcontact.com/gb/products/1289761>

Replacement battery for TP and WP 6000 touch panel



### PCB connector

PCB connector - MSTB 2,5/ 3-STF-5,08 - 1777992

<https://www.phoenixcontact.com/gb/products/1777992>



PCB connector, nominal cross section: 2.5 mm<sup>2</sup>, color: green, nominal current: 12 A, rated voltage (III/2): 320 V, contact surface: Tin, type of contact: Female connector, number of potentials: 3, number of rows: 1, number of positions: 3, number of connections: 3, product range: MSTB 2,5/...-STF, pitch: 5.08 mm, connection method: Screw connection with tension sleeve, screw head form: L Slotted, conductor/PCB connection direction: 0 °, locking clip: - without locking clip, plug-in system: COMBICON MSTB 2,5, locking: Screw locking, mounting: Screw flange, type of packaging: packed in cardboard

# Web panel - WP 6070-WVPS

1290800

<https://www.phoenixcontact.com/gb/products/1290800>

## Memory

Memory - MICROSDHC-16GB - 1154696

<https://www.phoenixcontact.com/gb/products/1154696>

Industrial grade 16 GB MicroSDHC 3DTLC



---

## Memory

Memory - MICROSDHC-32GB - 1154699

<https://www.phoenixcontact.com/gb/products/1154699>

Industrial grade 32 GB MicroSDHC 3DTLC



---

Phoenix Contact 2022 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd

Halesfield 13, Telford

Shropshire, TF7 4PG

01952 681700

[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)