

KEL - DPZ - B

Cable entry plates



Product description

The KEL-DPZ-B entry plates are designed for routing standard cables (without connectors) .

With an area of only 45 x 45 mm, up to 25 cables can be easily routed and sealed according to IP65.

Simply put a small slit in the thin membrane and push the cable through. Once the cable is through the membrane, it is immediately sealed and strain relieved.

ST Plugs (page 27) can be used for sealing pierced membranes if cables are removed.

Advantages

- Space saving shape
- Dual sealing of cables according to IP 66
- High packing density
- Assembly within seconds

Specification

Material	Frame: Polyamide Sealing plate: Elastomer
Flame class	UL-94 Vo, self-extinguishing
Protection class	IP 66
Temperature	- 40°C to + 90°C (static)
Properties	halogen-free, silicone-free
Cut-out dimensions	45 x 45 mm

Description	Type	Order No.	Number of cables	PU
	KEL - DPZ B 13	43794	8x 3.2 - 6.5 mm 4x 5.0 - 10.2 mm 1x 16 - 22 mm	10
	KEL - DPZ B 17	43796	10x 3.2 - 6.5 mm 4x 5.0 - 10.2 mm 2x 7.5 - 12 mm 1x 9.0 - 16.2 mm	10
	KEL - DPZ B 25	43798	25x 3.2 - 6.5 mm	10