

Crimp terminal, socket



FEATURES:


Vinyl fully-insulated

Double crimp

Funnel entry

SPECIFICATION:

Cross-section	0.5...1.5 mm ²
Colour	Red
Diameter (D)	4.3 mm
Material	Brass
Insulation material	Vinyl
Surface material	Tin-plated
Thickness (t)	0.4 mm
Temperature range	max. +105 °C
Length (L)	25 mm
Width (W)	4.65 mm



Art. Nr.

RND 465-00597