


## Climate control – 19" fan trays

### 19" fan 1 U with front switch



01194003



01197002


- Front-mounted illuminated mains switch on AC devices, coupled with additional rear mains outlet; mechanical strain relief for mains input and mains output cables
- Can be adapted to subracks
- Contact protection in accordance with DIN EN ISO 13857



#### Delivery comprises (ready to connect)

Item	Qty	Description
1	1	19" circulation fan, 1 U, top/base plate, St, 1 mm, finish AlZn, with perforation; front panel 1 U, Al, 3 mm, anodised
2	3 / 6	Fan, see Order Information
3a	1	AC version with mains switch, illuminated green; plug (mains input IEC 60320) incl. safety clamp for mechanical strain relief; coupled mains output socket (IEC 60320)
b3	1	DC version with mains switch and connecting cable, cable length 2.5 m


#### Order Information

	24 V <sub>DC</sub>	115 V <sub>AC</sub>	230 V <sub>AC</sub>
	Part no.	Part no.	Part no.
	<b>10713-111</b>	<b>10713-110</b>	<b>10713-108</b>

KTA44857

	<b>10713-115</b>	<b>10713-114</b>	<b>10713-112</b>
---	------------------	------------------	------------------

KTA44858



KTA45963

<b>Replacement fan 1 piece</b>	<b>20713-240</b>	<b>20713-244</b>	<b>20713-243</b>
<b>Side panel connecting bracket</b> between europacPRO subrack and fan, including fixing material kit, PU 4 pieces			<b>21101-954</b>
<b>Equipment cable SCHUKO/UTE</b> SCHUKO/UTE plug, IEC 60320 C13 socket, 2.5 m, 1 piece			<b>60103-131</b>
<b>Equipment cable, BS</b> British Standard plug, IEC 60320 C13 socket, 2.5 m, 1 piece			<b>60103-137</b>
<b>Equipment cable, USA</b> USA plug, IEC 60320 socket, 2 m, 1 piece			<b>60103-141</b>
<b>Mains cable, IEC</b> IEC 60320 C14 plug, IEC 60320 C13 socket, 2.5 m, 1 piece			<b>60197-053</b>



ServicePLUS see page 4.19

#### Technical data

Voltage	230 VAC		115 VAC		24 VDC
	50	60	50	60	-
Frequency in Hz					
Number of fans		3/6		3/6	3/6
Airflow volume in m <sup>3</sup> /h (3/6 fans)	440/845	520/1000	440/845	520/1000	506/970
Noise level in dB(A) (3/6 fans)	56.5/59.4	60.2/62.9	56.5/59.4	60.2/62.9	60.5/63.3
Power consumption in W (3/6 fans)	45/90	42/84	46.5/93	43.5/87	24/48
Max. stat. pressure in Pa	73	88	73	88	68
Permissible ambient temperature in °C	-40 ... +70 °C				
Lifespan in h L <sub>10</sub> 40 °C	43500				
Lifespan in h L <sub>10</sub> 55 °C	20000				

- Fan dimensioning, see page 4.18
- Replacement fans, see chapter Climate control - Accessories
- Versions with multiple fans see ServicePLUS configuration page 4.14