




CABLE/100M/ PUR/4X0.34/GR

Accessories



Product characteristics

Cable

Environment

Ambient temperature [°C] -40...90, cRUUs: max. 80 °C

Ambient temperature (moving) [°C] -25...90, cRUUs: max. 80 °C

Mechanical data

Drag chain suitability

Bending radius for flexible applications: min. 10 x cable diameter
max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s²
Travel speed: 5 m/s²
Bending cycles: > 2 million
Torsional strain: ± 180 °/m

Weight [kg] 3.419

Electrical connection

Connection

PUR cable / 100 m;
4 x 0.34 mm² (42 x Ø 0.1 mm); Ø 4.9 mm; not irradiated (can be recycled), halogen-free, resistant to welding sparks

Sheath colour

grey

Wiring

Core colours

BK black
BN brown
WH white
BU blue

Remarks

Pack quantity [piece] 1