



M12 FEMALE 90° B CODED SHIELD WIREABLE SCREW TERM.

5 POLE max. 0.75mm² 6-8mm PROFIBUS



M12
 Female 90°
 Field wireable (screw terminals)
 B-coded, 5-pole, shielded
 for PROFIBUS + Interbus

[Link to Product](#)

Illustration



Female



Product may differ from Image

Form

14031

Technical Data

Operating voltage	max. 60 V AC/DC
Operating current per contact	max. 4 A
Connection cross section	max. 0.75 mm ²
Sealing range (cable diameter)	6...8 mm
Protection	IP67 inserted and tightened (EN 60529)
Housing	CuZn, nickel plated

General data

Temperature range	-25...+85 °C
-------------------	--------------

Commercial data

country of origin	DE
customs tariff number	85369010
minimum order quantity	1