

## M23 FEMALE, 0° 19 POLE

PUR 16x0,34+3X0.75 GRAY, drag ch 5m

M23

Female straight

19-pole

19-pole used

for 8-way distribution boxes, 5-pole

Further cable lengths on request. Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.



### [Link to Product](#)

#### Illustration



15	white
7	gray/ pink
5	green
4	red/blue
	yellow
16	white/ green
8	gray
3	brown/ green
14	pink
17	white/ yellow
9	red
2	yellow/ brown
13	black
11	white/ gray
10	violet
1	gray/ brown
18	brown 1.0mm <sup>2</sup>
19	blue 1.0mm <sup>2</sup>
6	green/ yellow 1.0mm <sup>2</sup>
12	

## Female



Product may differ from Image

**Form**

23251

**Technical Data**

Operating voltage	max. 125 V AC/DC
Operating current per contact	max. 10 A
Locking of ports	Screw thread M23 × 1 mm
Protection	IP67 inserted and tightened (EN 60529)

**Cables**

Cable number	398
No./diameter of wires	16×0.34 + 3×0.75 mm <sup>2</sup>
Wire isolation	PVC
C-track properties	1 Mio.
Jacket Color	gray
Shore hardness outer jacket	85 ± 5A
Material (jacket)	PUR/PVC
Outer diameter	approx. 10.6 mm
Bend radius (fixed)	10 × outer Ø
Bend radius (moving)	12 × outer Ø
Temperature range (fixed)	-30...+80 °C
Temperature range (mobile)	-5...+70 °C

**General data**

Temperature range	-25...+85 °C, depending on cable quality
-------------------	--

**Commercial data**

country of origin	DE
customs tariff number	85444290
minimum order quantity	1