



868-915MHz Compressed Antenna

868-915MHz stubby Antenna



Electrical Specifications	
<i>Frequency Range:</i>	868-915MHz
<i>Nominal Impedance:</i>	50 ohm
<i>Maximum Input Power:</i>	50W
<i>Polarization:</i>	Omni
<i>VSWR</i>	≤1.5
<i>Connector:</i>	SMA male straight (SS) or Right angle (SR)

Mechanical Specifications	
<i>Material:</i>	Rugged Antenna
<i>Antenna dimensions:</i>	56mm x 8mm Straight 52mm x 8mm Right Angle
<i>Antenna weight:</i>	6 g
<i>Ambient temperature:</i>	-40 °C-+ 60 °C

Order Code:	ANT-SS900 ANT-SR900
--------------------	--------------------------------