

## Reducing sleeves E1 + E2 with slot

With groove

**ORION**<sup>®</sup>

### Execution:

- Surface hardness 58–60 HRC
- Core strength HV 950 N/mm<sup>2</sup>
- Hardness depth 0.8 mm ±0.2 mm
- Fully bronzed and precision-ground

<b>Art. no.</b>	<b>22778 234</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	22778234
<b>Clamping diameter</b>	25 mm
<b>Clamping diameter 2</b>	20 mm
<b>Collar diameter</b>	30 mm
<b>Length</b>	50 mm
<b>Collar width</b>	3 mm
<b>Clearance</b>	3.5 mm
<b>Length 2</b>	43.5 mm
<b>Groove width</b>	13 mm
<b>Gross Weight</b>	0.650 kg
<b>Product Group</b>	2AL



### EAN

4053625466122