

infinitely adjustable clamp, complete



Application:

For clamping workpieces. It is designed to withstand extremely high loads and is particularly suitable for clamping cutting tools and punches.

Version:

- made of steel, forged, tempered and galvanised.

Advantage:

- The infinitely variable adjustable clamp quickly spans various clamping heights without any additional support and requires little space on the machine table.



| | |
|---|------------------|
| Art. no. | 26223 065 |
| For table grooves according to DIN 650 | 20 mm |
| Min./max. clamping height | 0-85 mm |
| Clamping shoe length | 175 mm |
| Clamping shoe width | 60 mm |
| Bore diameter | 21 mm |
| Distance 2 | 80 mm |
| Distance | 40 mm |
| Distance 1 | 70 mm |
| Slot nut width of clamping screw | 20 mm |

EAN-Code

4020772074975