

Electronic micrometer

With large measuring range and interchangeable anvil

Mitutoyo

Application:

For measuring e.g. shank diameters, external dimensions of workpieces etc.

Execution:


- carbide-tipped measuring faces
- IP65
- HOLD (measured value storage)
- Friction coupling for consistent, repeatable measuring force
- ABS function

Advantage:

- Extra wide measuring range
- Interchangeable measuring anvil for a variable measuring range
- IP65
- Long battery life, approx. 2.4 years

Delivery:

Includes box, setting standard, gauge slides, adjustment wrench, battery



Art. no.	32017 388
Brand	MITUTOYO
Manufacturer Part Number	340-721
Display	Digital
Min./max. length measuring range in inches	18-24 in
Digit increment	0.0001 in
IP protection class	IP 40
Data transmission type	DIGIMATIC
Spindle clamping	Yes
Functions	ABS function, Hold-function (AE lock), Preset function, Automatic switch-off
Min./max. measurement force	10-15 N
Number of rechargeable batteries/batteries	1 PCS
Battery designation	1,5 V SR44
DIN	863
Measuring spindle increments	0.5 mm
Calibration Group	D
Gross Weight	10.300 kg
Product Group	3MA

EAN

4946368610559