

# PRODUCT SPECIFICATION

**Carl  
Kammerling**  
International

<b>Brand</b>	C.K
<b>Product Range</b>	Dextro VDE Slim Screwdrivers
<b>Catalogue number</b>	49242, 49243, 49244, 49245, 49283
<b>Date</b>	02/02/2017

## Range Description

A range of slim shafted VDE approved professional Electricians screwdrivers

## Features

- Slim shafted insulated blades - allow access to recessed screws and fixings
- Optimised grip for fingertip control and final torque down power
- Non-roll handle design – specifically designed to stop the screwdrivers rolling off non-flat surfaces
- Permanent tip type marking on the end of the handle for convenient blade type identification
- Additional blade type identification with colour coded handles
- Toughened high alloy steel blade offering the ultimate in wear resistance and performance
- Blade torque capacity up to 20% over the International standards requirement
- Chrome vanadium blade with black non peel tip finish for corrosion protection
- Precision machined tips for the ultimate screw fit and high torque output



T49242



T49243



T49244



T49245



T49283

Item Number	Item Description	EAN No	Commodity	Carton
-------------	------------------	--------	-----------	--------

			code	Qty
T49242-1	DextroVDE Slim S/Driver PH1x100	5013969032116	82054000	6
T49242-2	DextroVDE Slim S/Driver PH2x125	5013969032123	82054000	6
T49243-1	DextroVDE Slim S/Driver PZ1x100	5013969032093	82054000	6
T49243-2	DextroVDE Slim S/Driver PZ2x125	5013969032109	82054000	6
T49244-035	DextroVDE Slim S/Driver SLP 3.5x100	5013969032062	82054000	6
T49244-040	DextroVDE Slim S/Driver SLP 4.0x100	5013969032079	82054000	6
T49244-055	DextroVDE Slim S/Driver SLP 5.5x125	5013969032086	82054000	6
T49245-2	DextroVDE Slim S/Driver MOD2x125	5013969032130	82054000	6
T49283	DextroVDE Slim S/Driver SLP/PZD Set/5 contains SL3.5x100, SL4.0x100, SL5.5x125, PZ1x100, PZ2x125	5013969032055	82054000	18

<p>Technical product information</p>	<p><b>Blade/Shaft</b></p> <p>Made from chrome molybdenum vanadium steel, hardened to 57-59 HRC, black non peel finish.</p> <p><b>Handle</b></p> <p>The handle core is polypropylene, injection moulded around the blade with a TPE soft grip over-mould. The handles are shatterproof down to -35° C.</p> <p><b>Dimensions</b></p> <table border="1" data-bbox="488 1102 1252 1459"> <thead> <tr> <th>Dimensions (mm)</th> <th>Handle length</th> <th>Blade length</th> <th>Blade Dia</th> <th>Tip thickness</th> </tr> </thead> <tbody> <tr> <td>T49242-1</td> <td>95</td> <td>100</td> <td>5.5</td> <td>-</td> </tr> <tr> <td>T49242-2</td> <td>107</td> <td>125</td> <td>6.5</td> <td>-</td> </tr> <tr> <td>T49243-1</td> <td>95</td> <td>100</td> <td>4.5</td> <td>-</td> </tr> <tr> <td>T49243-2</td> <td>107</td> <td>125</td> <td>6.5</td> <td>-</td> </tr> <tr> <td>T49244-035</td> <td>95</td> <td>100</td> <td>3.5</td> <td>0.6</td> </tr> <tr> <td>T49244-040</td> <td>95</td> <td>100</td> <td>4</td> <td>0.8</td> </tr> <tr> <td>T49244-055</td> <td>107</td> <td>125</td> <td>5.5</td> <td>1.0</td> </tr> <tr> <td>T49245-2</td> <td>107</td> <td>125</td> <td></td> <td>-</td> </tr> </tbody> </table>	Dimensions (mm)	Handle length	Blade length	Blade Dia	Tip thickness	T49242-1	95	100	5.5	-	T49242-2	107	125	6.5	-	T49243-1	95	100	4.5	-	T49243-2	107	125	6.5	-	T49244-035	95	100	3.5	0.6	T49244-040	95	100	4	0.8	T49244-055	107	125	5.5	1.0	T49245-2	107	125		-
Dimensions (mm)	Handle length	Blade length	Blade Dia	Tip thickness																																										
T49242-1	95	100	5.5	-																																										
T49242-2	107	125	6.5	-																																										
T49243-1	95	100	4.5	-																																										
T49243-2	107	125	6.5	-																																										
T49244-035	95	100	3.5	0.6																																										
T49244-040	95	100	4	0.8																																										
T49244-055	107	125	5.5	1.0																																										
T49245-2	107	125		-																																										
<p>Standards compliance</p>	<p><b>Electrical safety</b></p> <p>Fully approved and independently audited by the German VDE institute to VDE 0682/201:2005 01 IEC 60900:2012</p> <p><b>Dimensional and performance</b></p> <p>Slotted screwdrivers – DIN ISO 2380 PZD/SDV/PH Screwdrivers – DIN ISO 8764</p>																																													
<p>User health and safety</p>	<p>Users and bystanders are advised to wear safety goggles</p>																																													

information	
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	Dextro Screwdrivers are guaranteed for life against imperfect materials or workmanship Normal wear and tear or damage caused through inappropriate use is not covered
Country of origin	Germany

## Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T49242-1	30	25	195	46	30	25	195	46
T49242-2	35	30	232	74	35	30	232	74
T49243-1	30	25	195	46	30	25	195	46
T49243-2	35	30	232	80	35	30	232	80
T49244-035	30	25	195	39	30	25	195	39
T49244-040	30	25	195	43	30	25	195	43
T49244-050	35	30	232	74	35	30	232	74
T49245-2	35	30	232	80	35	30	232	80
T49283	225	43	300	635	225	43	300	635

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T49242-1	85	50	225	330		
T49242-2	95	60	265	514		
T49243-1	85	50	225	330		
T49243-2	95	60	265	550		
T49244-035	85	50	225	288		
T49244-040	85	50	225	312		
T49244-050	95	60	265	514		
T49245-2	95	60	265	550		
T49283	420	255	610			

## Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T49242-1							54	Box
T49242-2							70	Box
T49243-1							54	Box
T49243-2							70	Box
T49244-035							54	Box

T49244-040							54	Box
T49244-050							70	Box
T49245-2							70	Box
T49283								Box