

PRODUCT SPECIFICATION

Brand	C.K
Product Range	Hand and Head Torches
Catalogue number	9410, 9505, 9510, 9520, 9530R, 9540R, 9710R, 9621, T9420, T9421R, T9422R, T9612, T9730T, T9730RT
Date	16/07/2018

<p>Range Description Hand and Head Torches</p>	
<p>Features</p> <p>9510</p> <ul style="list-style-type: none"> • High power 120 lumen CREE XR-E Q5 LED • 3 lighting modes: High, Dimmed, Flash • One-handed Rapid Slide Focus mechanism (RSF) - Spot (x1) to Flood (x10) • Beam intensifying plano-convex optical lens • Robust high grade aluminium body • Water & dirt resistant, certified to IPX4 • Battery life: High - 6hrs, Dimmed - 16hrs • Battery 3 x AAA (Not supplied) 	
<p>9520</p> <ul style="list-style-type: none"> • High power 150 lumen CREE XR-E Q5 LED • 3 lighting modes: High, Dimmed, Flash • One-handed Rapid Slide Focus mechanism (RSF) - Spot (x1) to Flood (x30) • Beam intensifying plano-convex optical lens • Robust high grade aluminium body • Water & dirt resistant, certified to IPX4 • Battery life: High - 5hrs, Dimmed - 14hrs • Battery 3 x AAA (Not supplied) 	
<p>T9505</p> <ul style="list-style-type: none"> • High power 100 lumen CREE XP-E R3 LED • 3 lighting modes: high, dimmed, flash • One-handed rapid slide focus mechanism – Spot (x1) to Flood (x6) • Beam intensifying plano-convex optical lens • Robust high grade aluminium body • Water & dirt resistant, certified to IPX4 • Battery life: High – 3hrs, Dimmed – 7hrs • Size: 98 x 26mm 	

T9530R

- High power 300 lumen CREE XM-L T6 LED
- 3 lighting modes: high, dimmed, flash
- One-handed rapid slide focus mechanism – Spot (x1) to Flood (x6)
- Beam intensifying plano-convex optical lens
- Robust high grade aluminium body
- Water & dirt resistant, certified to IPX4
- Battery life: High – 3.5hrs, Dimmed – 8hrs
- Size: 131 x 34mm



T9540R

- High power 400 lumen CREE XM-L T6 LED
- 3 lighting modes: high, dimmed, flash
- Compound spot & flood beam
- Extra large 40mm aluminium reflector
- Robust high grade aluminium reflector
- Water & dirt resistant, certified to IPX4
- Battery life: High – 3.5hrs, Dimmed – 7hrs
- Size: 235 x 55mm



T9410

- 8 Super bright LEDs
- Wide flood beam
- 180° rotating magnetic pocket clip
- Water & dirt resistant, certified to IPX4
- Battery life: 8hrs
- Size: 160 x 26mm



T9710R

- High performance 600 Lumen Epistar COB LED
- Power: 10W
- Wide 120° flood beam
- Magnetic base
- Vertical and horizontal rotation
- Water & dirt resistant, tested to IP65
- Battery life: 3hrs
- Size: 147 x 168 x 240mm



T9621

- High Power 200 Lumen Cree XM-L T6 LED
- 3 Lighting modes: high, dimmed, flash
- One-handed rapid slide focus mechanism - spot (x1) to flood (x7)
- Beam intensifying plano-convex optical lens
- Robust high-grade aluminium body
- Adjustable head lamp swivels through 90°
- Water & dirt resistant, tested to IPX4
- Battery life: high - 4hrs, dimmed - 10hrs, flash - 4hrs



T9621R

- High Power 200 Lumen Cree XM-L T6 LED
- 3 Lighting modes: high, dimmed, flash
- One-handed rapid slide focus mechanism - spot (x1) to flood (x7)
- Beam intensifying plano-convex optical lens
- Robust high-grade aluminium body
- Adjustable head lamp swivels through 90°
- Water & dirt resistant, tested to IPX4

Battery life: high - 5hrs, dimmed - 12hrs, flash - 5 hrs



T9420

- Super bright COB-LED
- Wide flood beam
- End torch light
- Magnetic pocket clip
- 4 lighting modes: High, dimmed, flash, torch
- Size: 162 x 26mm



T9421R

- High Power 240 Lumen COB-LED with additional torch light
 - Wide flood beam
 - 3 Lighting modes: high, dimmed, torch light
 - Swivelling magnetic base
 - Integrated hanging hook and belt clip
 - Water & dirt resistant, tested to IP54
 - Micro USB rechargeable (supplied with USB cable & UK mains charger)
 - Battery life indicator
- Battery life: high - 3hrs, dimmed - 10hrs, torch light - 25hrs



T9422R

- Super bright COB-LED
 - Wide flood beam
 - 3 Lighting modes: high, dimmed, torch light
 - Swivelling magnetic base and magnetic back
 - Integrated hanging hooks
 - Water & dirt resistant, tested to IP54
 - Micro USB rechargeable (supplied with USB cable & UK mains charger)
 - Battery life indicator
- Battery life: high - 3hrs, dimmed - 10hrs, torch light - 25hrs



T9612

- Super bright COB-LED
- Wide flood beam
- End torch light
- Magnetic pocket clip
- 4 lighting modes: High, dimmed, flash, torch
- Size: 162 x 26mm



T9730R

- High Power 2700 Lumen COB LED's
- 3 Lighting modes: high, medium, dimmed
- 120° wide flood beam
- Rechargeable (supplied with UK mains charger & car charger)
- Water & dirt resistant, tested to IP65
- Easy to store and transport with secure locking mechanism

Battery life: high - 2.5hrs, medium - 5hrs, dimmed - 7.5hrs

**T9730RT**

- Heavy duty sturdy construction
- Quick height adjustment (max height: 1.45m)
- Secure locking mechanism
- Convenient foldaway legs

Compact storage



Item Number	Item Description	EAN No	Commodity code	Carton Qty
T9510	C.K CREE LED Hand Torch 120 Lumens	5013969977448	8513100000	6
T9520	C.K CREE LED Hand Torch 150 Lumens	5013969977431	8513100000	6
T9505	C.K CREE LED Hand Torch 100 Lumens	5013969977523	8513100000	6
T9530R	C.K CREE LED Hand Torch 300 Lumens	5013969977530	8513100000	6
T9540R	C.K CREE LED Hand Torch 400 Lumens	5013969977547	8513100000	6
T9410	C.K LED Pocket Inspection Light 120 Lumens	5013969977479	8513100000	12
T9710R	C.K Rechargeable LED Flood Light 600 Lumens	5013969977493	9405403960	1
T9621	LED Head Torch 200 Lumens	5013969978988	8513100000	6
T9621R	LED Rechargeable Head Torch 200 Lumens	5013969978995	8513100000	6

T9420	COB-LED Pocket Inspection Light 120 Lumens	5013969244649	8513100000	6
T9421R	COB-LED Rechargeable Inspection Light 240 Lumens	5013969244656	8513100000	6
T9422R	COB-LED Rechargeable Inspection Light 420 Lumens	5013969244663	8513100000	6
T9612	LED Head Torch 150 Lumens	5013969244670	8513100000	4
T9730R	COB-LED 30W Rechargeable Flood Light 2700 Lumens	5013969977677	9405403990	1
T9730RT	Tripod for 30W Rechargeable Flood Light T9730R	5013969981407	9405403990	1

Technical product information	
Standards compliance	None applicable
User health and safety information	None applicable
RoHS/WEEE compliance	This product range is fully Compliant with the RoHS and WEEE regulations
Material safety data	None applicable
Warranty	C.K Torch products are guaranteed for 3 years against imperfect materials or workmanship Normal wear and tear or damage caused through inappropriate use is not covered
Country of origin	China

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T9510	40	40	133	169	160	125	40	138
T9520	30	30	107	104	205	135	55	223
T9505	25	97	30	80	123	27	177	86
T9530R	33	139	38	280	158	54	205	362
T9540R	55	232	53	516	182	67	330	657
T9410	15	160	34	59	107	40	235	60
T9710R	140	240	70	1168	215	120	120	1283
T9621	-	-	-	129	131	205	105	180
T9621R	200	230	110	208	200	230	110	337
T9420	30	20	160	46	80	30	250	60
T9421R	52	37	170	281	155	50	260	305
T9422R	55	30	220	378	150	50	290	407
T9612	130	60	190	120	130	60	190	199

T9730R								
T9730RT								

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T9510	23	Clamshell	10	Card			50	box
T9520	31	Clamshell	10	Card			60	box
T9505	19	Clamshell	11	Card			64	box
T9530R	64	Clamshell	15	Card			181	box
T9540R	111	Clamshell	27	Card			282	box
T9410	19	Clamshell	7	Card			121	box
T9710R	99	Box	8	Card			1283	Box
T9621		Clamshell		Card			180	Box
T9621R	96	Clamshell	33	Card			250	Box
T9420	10	Clamshell	6	Card				
T9421R	18	Clamshell	8	Card				
T9422R	20	Clamshell	10	Card				
T9612	21	Clamshell	58	Card				
T9730R								
T9730RT								

Document History:
Created Date 27/08/2014
Amended 14/10/2015 – torches and head lamps now certified to IPX4