

# Europa Series Terminal Blocks



## 1500

- Connection:** conductor size 0.5 - 6.0 mm<sup>2</sup> (with wire protector)  
 conductor size 0.5 - 10.0 mm<sup>2</sup> (without wire protector)
- Fixing:** by screw or rivet size Ø 4.3 mm
- Torque screw:** M4: ⤵ max. 1.2 Nm
- Stripping length:** 8 - 8.5 mm
- Important approvals:** VDE, UL
- Accessories:** covers (page 83), strain reliefs, marking labels (page 85)
- Upon request:** 7 - 11 pole, printing, different polyamides (in particular glow wire to EN 60335-1), different screws

Description	Item	Order Number	PU
<b>with Wire Protectors</b>			
1 pole	1500/1 DS	127101	500
2 pole	1500/2 DS	127102	500
3 pole	1500/3 DS	127103	500
4 pole	1500/4 DS	127104	400
5 pole	1500/5 DS	127105	60
6 pole	1500/6 DS	127106	50
12 pole	1500/12 DS	127112	25
<b>without Wire Protectors</b>			
1 pole	1500/1	127001	500
2 pole	1500/2	127002	500
3 pole	1500/3	127003	500
4 pole	1500/4	127004	400
5 pole	1500/5	127005	60
6 pole	1500/6	127006	50
12 pole	1500/12	127012	25

