



LED PL 2G11 220-240V 24W 4000K Frosted

Item no. 80100038477

Bailey LED PL Lamp Tube 2G11 24W Cool White 4000K CRI80-89 Frosted 2150lm 176-265V AC 160D 39x542mm

Request: [✉](#)

Specifications

Product group	LED lamp
Brand	Bailey
Serie	LED PL
Part no. brand	80100038477
Lamp shape	Tube
Base	2G11
Finish	Frosted
Nominal voltage (V)	176
Nominal voltage upper limit (V)	265
Nominal power (W)	24
Nom. Stroom (mA)	150
Luminous flux (lm)	2150
Colour	Cool White
Colour temperature (K)	4000
Colour rendering index CRI	80-89
Colour code	840
Dimmable	No
Lifespan (h)	35000
Beam angle (°)	160
Degree of protection (IP)	IP20
Energy efficiency class	A+
Diameter (mm)	39
Length (mm)	542
EAN-code Bailey	8714681384770