

PORTALÁMPARAS DE BAQUELITA
BAQUELITE LAMP-HOLDER



PORTALÁMPARAS DE BAQUELITA / BAQUELITE LAMP-HOLDER



Código:	EM 09 080	
FORMA EXTERNA Y DIMENSIONES / EXTERNAL SHAPE AND DIMENSIONS	FORMA/SHAPE	DIMENSIONES / DIMENSIONS
	161: Liso / <i>Plain</i>	Ø 39 x 54 mm
	162: Roscado / <i>Threaded</i>	Ø 40 x 58 mm
	163. Roscado con tope / <i>Threaded with stop ring.</i>	Ø 40 X 54 mm
DIRECTIVA / DIRECTIVE	2014/35/UE REBT 2002 – Reglamento de Baja Tensión/ <i>Spanish Low Voltage Regulations</i>	
CARACTERÍSTICAS ELÉCTRICAS ELECTRICAL CHARACTERISTICS	Casquillo / <i>Cap:</i>	E-27
	Intensidad / <i>Current:</i>	4 A
	Tensión / <i>Voltage:</i>	250 V
	Frecuencia / <i>Frequency:</i>	50 / 60 Hz
MATERIAL	Baquelita / <i>Baquelite</i>	
MÉTODO DE FIJACIÓN / FIXING METHOD	Tuerca/ Nut	M10 x 1,0
	Con tornillo antirotación / <i>with antirotating screw</i>	
TIPO DE BORNE / TERMINAL TYPE	Borne con tornillo / <i>Screw-type terminal</i>	
RESISTENCIA DE AISLAMIENTO / ISOLATION RESISTANCE	>4 M Ω	
RIGIDEZ DIELECTRICA / DIELECTRIC STRENGTH	1500 V	
NORMAS APLICADAS / APPLIED STANDARD	EN 60238	
Código:	EM 09 080	