


Data sheet Gebo G316 / Gewindefittings aus Edelstahl / Stainless steel threaded fittings  
Code 6241

Reduziernippel – A/I / Hexagon Bushing – M/F

- Material: 1.4408
- Legierungsbestandteile / Alloying components in %:  
C ≤ 0,07 – Cr 18,0-20,0 – Ni 9,0-12,0 – Mo 2,0-2,5
- Anschlussgewinde/Connection thread DIN EN 10226 (ISO 7/1)



2



Size (1x2)	Code	mm				kg
		L	SW	e		
1/4" x 1/8"	6241-014018	16,0	14,0	16,2	hex.	0,007
3/8" x 1/8"	6241-038018	16,5	18,0	20,8	hex.	0,017
3/8" x 1/4"	6241-038014	16,5	18,0	20,8	hex.	0,014
1/2" x 1/8"	6241-012018	20,0	22,0	25,4	hex.	0,030
1/2" x 1/4"	6241-012014	20,0	22,0	25,4	hex.	0,020
1/2" x 3/8"	6241-012038	20,0	22,0	25,4	hex.	0,019
3/4" x 1/8"	6241-034018	21,0	27,5	31,6	hex.	0,040
3/4" x 1/4"	6241-034014	21,0	27,5	31,6	hex.	0,045
3/4" x 3/8"	6241-034038	21,0	27,5	31,6	hex.	0,038
3/4" x 1/2"	6241-034012	21,0	27,5	31,6	hex.	0,031
1" x 1/4"	6241-100014	24,5	34,5	39,8	hex.	0,077
1" x 3/8"	6241-100038	24,5	34,5	39,8	hex.	0,096
1" x 1/2"	6241-100012	24,5	34,5	39,8	hex.	0,078
1" x 3/4"	6241-100034	24,5	34,5	39,8	hex.	0,054
1 1/4" x 3/8"	6241-114038	27,5	43,0	49,7	hex.	0,114
1 1/4" x 1/2"	6241-114012	27,5	43,0	49,7	hex.	0,139
1 1/4" x 3/4"	6241-114034	27,5	43,0	49,7	hex.	0,095
1 1/4" x 1"	6241-114100	27,5	43,0	49,7	hex.	0,086
1 1/2" x 3/8"	6241-112038	28,5	49,0	56,6	hex.	0,212
1 1/2" x 1/2"	6241-112012	28,5	49,0	56,6	hex.	0,194
1 1/2" x 3/4"	6241-112034	28,5	49,0	56,6	hex.	0,168
1 1/2" x 1"	6241-112100	28,5	49,0	56,6	hex.	0,125
1 1/2" x 1 1/4"	6241-112114	28,5	49,0	56,6	hex.	0,097
2" x 1/2"	6241-200012	33,0	61,0	70,4	hex.	0,224
2" x 3/4"	6241-200034	33,0	61,0	70,4	hex.	0,230
2" x 1"	6241-200100	33,0	61,0	70,4	hex.	0,221
2" x 1 1/4"	6241-200114	33,0	61,0	70,4	hex.	0,231
2" x 1 1/2"	6241-200112	33,0	61,0	70,4	hex.	0,202
2 1/2" x 1"	6241-212100	37,0	76,0	82,3	oct.	0,328
2 1/2" x 1 1/4"	6241-212114	37,0	76,0	82,3	oct.	0,321
2 1/2" x 1 1/2"	6241-212112	37,0	76,0	82,3	oct.	0,320
2 1/2" x 2"	6241-212200	37,0	76,0	82,3	oct.	0,352
3" x 1 1/4"	6241-300114	40,0	90,0	97,4	oct.	0,472
3" x 1 1/2"	6241-300112	40,0	90,0	97,4	oct.	0,503
3" x 2"	6241-300200	40,0	90,0	97,4	oct.	0,510
3" x 2 1/2"	6241-300212	40,0	90,0	97,4	oct.	0,469
4" x 2"	6241-400200	46,0	115,0	124,5	oct.	1,711
4" x 2 1/2"	6241-400212	46,0	115,0	124,5	oct.	0,832
4" x 3"	6241-400300	46,0	115,0	124,5	oct.	0,983