

Accessory

PICO-LPG-635-660-BOX
Order Number: 70144864

Main Parameters (*)	min	typ	max	Unit
Operating Temperature	-20		40	°C
Storage Temperature	-50		50	°C

Optical Parameters

LB Rating	630-711 DIR LB5, 648-708 D LB5 + IR LB6, 651-704 D LB5 + IR LB7, 654-699 D LB5 + IR LB8, 712-713 DIR LB4, 714-717 DIR LB3
Lens Color	Aqua

Mechanical Parameters

Material	Plastic
Weight	150 g

(*) Over the complete operating temperature range

Features



- Laser glasses for red wavelengths
- Incl. wall holder
- Stickers with mandatory and hazard sign

Picture



Safety Label



Valid Revision

| 28-OCT-2020