



Order symbol: TA090706
Product nbr: 5814038
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074011466
EI. number:
Finland: 3438267
Electric No. Denmark: 8212045211
Electric No. Sweden: 5814038

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Sample photo

Dimensions:	Length	Width	Height	Accessories:	
mm:	95	65	60	DRM 50	DIN-15 Mounting rail
inch:	3.7	2.6	2.4	FP 10674	
				DPS 14553	Grey sealing plug set

Materials:		Rating:	
Material:	ABS	Ingress Protection (EN 60529):	IP65
Base colour:	RAL 7035 -light grey	Impact Resistance (EN 62262):	IK07
Cover screws material:	Polyamide	Electrical insulation:	Totally insulated
Cover colour:	RAL 7035 -light grey	Halogen free (DIN/VDE 0472, Part 815):	1
Cover screws colour:	Grey	Flammability Rating:	UL 94 HB
Gasket material:	Polyurethane	Glow Wire Test (IEC 695-2-1) °C:	650

Temperatures:		Certificates:	
Temperature °C (short term):	-40 ... 80 °C	SGS Fimko	
Temperature °C (continuous):	-40 ... 60 °C		
Temperature °F (short term):	-40 ... 175 °F		
Temperature °F (continuous):	-40 ... 140 °F		

Accessories:	
MP 0907	Mounting plate

