### **KNIPEX** Quality – Made in Germany



## **Product information**

# 95 36 250

## Cable Cutter

(ratchet action)

IEC 60900 DIN EN 60900



- For cutting copper and aluminium single conductors as well as multiple stranded cables
- Not suitable for steel wire, wire ropes and fine-stranded (highly flexible) conductors
- Precision-ground, hardened blades
- Clean and smooth cut without crushing and deformation
- One-hand operation using ratchet principle
- Little handforce required due to very high transmission ratio
- Two-stage ratchet drive for easy cutting
  Simple handling as a result of low weight and compact design can be used even in confined areas
- Pinch guard prevents operators' fingers being pinched
- High-grade special tool steel, forged, oil-hardened

<u></u>
<u>₹</u>1000 V MM

#### General

Article No.	95 36 250
EAN	4003773026884
Pliers	black lacquered
Handles	insulated with multi-component grips, VDE-tested
Weight	652 g
Dimensions	250 x 115 x 20 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Cutting capacity copper cable, multiple- stranded	240 mm <sup>2</sup>
Cutting capacity copper cable, multiple- stranded	Ø 32 mm
MCM	500
VDE tested	yes

technical change and errors excepted





Ratchet principle and two-stage ratchet drive for easier cutting